


DATA SHEET

CoaXPress CXP-6 Interface Cable

4 BNC to 4 DIN 1.0/2.3 screw lock, 10.0 m

Order code:
13317

V1.0.0
2018-June-07




Connector 1
4 BNC

Cable
Four Bundle

Connector 2
4 DIN 1.0/2.3 Screw lock

Cable label



Specifications

Feature	Specification
Length	10.0 m ± 100 mm
Diameter	13.64 mm
Bandwidth	4.5 GHz
Static bending radius	136 mm
Outer Jacket	TPE
Temperature range	-30 °C to +75 °C
Regulations	RoHS