



DATA SHEET

Interface cable


 IEEE 1394b 9-pin screw lock
 to IEEE 1394a 6-pin latch, 4.5 m


 Order code:
 K1200171

 V1.0.0
 2016-Sep-28

Connector 1



 IEEE 1394b 9-pin connector with
 die cast shell, screw lock


Mating Face View


Cable
Connector 2

 IEEE 1394a 6-pin connector
 with latch


Mating Face View

Cable label

Wiring diagram

Note

Unit in technical drawings is [mm].

Specifications

Feature	Specification
Length	4.5 m ± 50 mm
Diameter	7.2 mm
Classification	Industrial suitability for static applications
Static bending radius	43.2mm
Dynamic bending radius	For static applications only
Temperature range	On request
Regulations	UL20276, RoHS 2011/65/EU, REACH