


DATA SHEET

## Interface cable

IEEE 1394b 9-pin screw lock  
to IEEE 1394a 6-pin standard, 4.5 m


Order code:  
K1200288

V1.0.0  
2016-Sep-28




### Connector 1

IEEE 1394b 9-pin connector with  
die cast shell, screw lock




Mating Face View



### Cable


### Connector 2

IEEE 1394a 6-pin connector




Mating Face View

### Cable label



### Wiring diagram



### Note

Unit in technical drawings is [mm].

### Specifications

Feature	Specification
Length	4.5 m ± 100 mm
Diameter	4.8 mm
Classification	Industrial suitability for static applications
Static bending radius	28.8 mm
Dynamic bending radius	For static applications only
Temperature range	On request
Compliance	UL20276, RoHS 2011/65/EU, REACH