

IEEE 1394a

FW-6port-Hub



IEEE 1394a FireWire Hub with 6 Ports, Metal Housing

FW-6port-Hub can be used for a 6 Port FireWire IEEE 1394a Hub or as a repeater.

With the metal case it is extremely robust and optimal for industrial application.

Highlights

- Compatible with IEEE 1394a
- Up to 400 Mbps
- Easy plug & play, no driver required
- Power plug for optional bus power
- Inclusive power supply (12 V, 1.5 A)
- Compatible with all Allied Vision IEEE 1394a cameras
- Compatible with all Allied Vision Software Packages¹

¹ For details refer to the corresponding releases

Technical Specifications

Feature	Description
Ports	6 x IEEE 1394a
Speed	Full Duplex Data Rate at 100/200/400 Mbps
OS support	
Compliance	CE, FCC, RoHS
External power	Power Supply 12 VDC, 1.5 A Hub can be powered from 8VDC to 30VDC at 12V Power connector as well at the 12 Volt line of the PC connector
Dimensions (L x W x H)	150 x 70 x 30 mm
Mass	400 g
Operating temperature	+0°C to +50°C

Ordering information:

Hub 6-port 1394a	IEEE 1394a 6-port Hub with power supply, metal housing	K0000374
------------------	--	----------