





Model without hardware options

Alvium FP3-1242 STP

- IMX545 CMOS sensor
- 12.4 MP resolution
- ALVIUM image processing
- FPD-Link III interface
- Various hardware options

Robust CSI-2 based Alvium cameras with FPD-Link III interface

Benefit from greater flexibility in cable lengths

Alvium FP3 STP cameras with FPD-Link III (Flat Panel Display Link) interface have been designed to overcome the limitations of standard CSI-2 cameras. The closed housing CSI-2 based cameras come with integrated serializer and a rugged HSD STP connector for cable lengths up to 10 meters. This connection can also be used to power cameras (Power over STP), enabling single cable solutions.

To operate Alvium FP3 cameras on your vision system, Allied Vision provides different access modes: - GenlCam for CSI-2 Access controls the camera by GenlCam features, using the Alvium CSI-2 driver and CSI-2 transport layer (TL) directly. All Alvium FP3 STP models with equivalent 1800 C models are supported. Please find FAQs and installation instructions in the Getting Started with GenlCam for CSI-2 application note. - Direct Register Access (DRA) to control the cameras via registers for advanced users. - Video4Linux2 Access allows to control the cameras via established V4L2 API and applications like GStreamer and OpenCV. Open-source CSI-2 drivers are available on GitHub for different boards and systems on chip (SoCs).

In addition to lens mount and housing options, see Customization and OEM Solutions webpage for additional options.



Specifications	
Interface	FPD-Link III, based on MIPI CSI-2, up to 4 lanes
Resolution	4128 (H) × 3008 (V)
Spectral range	300 to 1100 nm
Sensor	Sony IMX545
Sensor type	CMOS
Shutter mode	GS (Global shutter)
Sensor size	Type 1/1.1
Pixel size	2.74 μm × 2.74 μm
Lens mounts (available)	C-Mount, CS-Mount
Max. frame rate at full resolution	Mainly depends on hardware and register settings.
ADC	12 Bit
Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

Output	
Bit depth	12-bit
YUV color pixel formats	YUV422 8-bit (UYVY) [MIPI CSI-2 (FOURCC)]
RGB color pixel formats	RBG888 (RGB3) [MIPI CSI-2 (FOURCC)]
Raw pixel formats	RAW8 (GREY), RAW10 (Y10), RAW12 (Y12) [MIPI CSI-2 (FOURCC)]


General purpose inputs/outputs (GPIOs)

TTL I/Os 2 programmable GPIOs

Operating conditions/dimensions	
Operating temperature	-20 °C to +65 °C (housing)
Power requirements (DC)	5 VDC over MIPI CSI-2
Power consumption	Value for the integrated serializer adds to CSI-2 model value
Mass	70 g
Body dimensions ($I \times W \times H$ in mm)	41 × 29 × 29



Quantum efficiency





Features

Image control: Auto

- Auto exposure
- Auto gain
- Auto white balance (color models)

Image control: Other

- Black level
- Color transformation (incl. hue, saturation; color models)
- De-Bayering up to 5×5 (color models)
- DPC (defect pixel correction)
- FPNC (fixed pattern noise correction)
- Gamma
- Reverse X/Y
- ROI (region of interest)

Camera control

- Acquisition frame rate
- Firmware update in the field
- I/O and trigger control
- Temperature monitoring



Technical drawing

