







- IMX422 CMOS sensor
- 2.0 MP resolution
- ALVIUM image processing
- GMSL2 interface
- Various hardware options

Model without hardware options

Robust CSI-2 based Alvium cameras with GMSL2 interface

Benefit from greater flexibility in cable lengths

Alvium GM2 Coax cameras with GMSL2 interface have been designed to overcome the limitations of standard CSI-2 cameras. The closed housing CSI-2 based cameras come with integrated serializer and a rugged coaxial-based FAKRA connector for thin coax cables. With Alvium GM2 Coax, cable lengths up to 15 meters are possible. The coax cable can also be used to power the camera (Power over coax) enabling a single cable solution.

To operate Alvium GM2 cameras on your vision system, Allied Vision provides different access modes: - **GenlCam for CSI-2 Access** controls the camera by GenlCam features, using the Alvium CSI-2 driver and CSI-2 transport layer (TL) directly. All Alvium GM2 Coax models with equivalent 1800 C models are supported. Please find FAQs and installation instructions in the Getting Started with GenlCam for CSI-2 application note. - Direct Register Access (DRA) to control the cameras via registers for advanced users. - Video4Linux2 Access allows to control the cameras via established V4L2 API and applications like GStreamer and OpenCV. Open-source CSI-2 drivers are available on GitHub for different boards and systems on chip (SoCs).

In addition to lens mount and housing options, see Customization and OEM Solutions webpage for additional options.



Specifications

Interface	GMSL2, based on MIPI CSI-2, up to 4 lanes
Resolution	1632 (H) × 1248 (V)
Spectral range	300 to 1100 nm
Sensor	Sony IMX422
Sensor type	CMOS
Shutter mode	GS (Global shutter)
Sensor size	Туре 1/1.7
Pixel size	4.5 μm × 4.5 μm
Lens mounts (available)	C-Mount, CS-Mount
Max. frame rate at full resolution	Mainly depends on hardware and register settings.
ADC	12 Bit
Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

Output	
Bit depth	8-bit, 10-bit, 12-bit; Adaptive (10-bit, 12-bit)
Monochrome pixel formats	PFNC: Mono8, Mono10, Mono10p, Mono12, Mono12p
YUV color pixel formats	PFNC: YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr CSI-2: YUV422 8-bit FOURCC: UYVY
RGB color pixel formats	PFNC: RGB8 (default), BGR8 CSI-2: RGB888 (default) FOURCC: RGB3
Raw pixel formats	PFNC: BayerRG8, BayerGR10, BayerRG10p, BayerGR12, BayerRG12p CSI-2: RAW8, RAW10, RAW12 FOURCC: GREY, Y10, Y12

General purpose inputs/outputs (GPIOs)

TTL I/Os

2 programmable GPIOs

Operating conditions/dimensions

Operating temperature	-20 °C to +65 °C (housing)
Power requirements (DC)	5 VDC over MIPI CSI-2



Power consumption Value for the integrated serializer adds to CSI-2 model value.

Mass

70 g Body dimensions (L \times W \times H in mm) 41 \times 29 \times 29

Features

Image control: Auto

- Auto exposure
- Auto gain
- Auto white balance (color models)

Image control: Other


- Black level
- Color transformation (incl. hue, saturation; color models)
- De-Bayering up to 5×5 (color models)
- DPC (defect pixel correction)
- Gamma
- Reverse X/Y
- ROI (region of interest)

Camera control


- Acquisition frame rate
- Firmware update in the field
- I/O and trigger control
- Temperature monitoring





Technical drawing











13 ±0.1

20 ±0.1

M3 - 2.2 ∓ (2x)

 \odot

\$

