



Alvium

1800 U-235c

- IMX174 CMOS sensor
- ALVIUM image processing
- USB3 Vision
- Various hardware options

Hardware option: Open Housing C-Mount Standard

Alvium 1800 U – Your entry into high-performance imaging

Industrial USB cameras with attractive price-performance ratio

Alvium 1800 U-235 with Sony IMX174 runs 155.0 frames per second at 2.4 MP resolution.

Alvium 1800 U is your entry into high-performance imaging with ALVIUM® Technology for industrial applications. Equipped with the newest generation of sensors, these small and lightweight cameras deliver high image quality and frame rates at the best price-performance ratio. With its USB3 Vision compliant interface and industrial-grade hardware, it is your workhorse for different machine vision applications whether it is on a PC-based or an embedded system.

Easy software integration with **Vimba X** and compatibility to the most popular third party image-processing libraries.

In addition to lens mount and housing options, see [Customization and OEM Solutions webpage](#) for additional options.

Specifications

| | |
|------------------------------------|-------------------------------|
| Product code | 18068 |
| Interface | USB3 Vision |
| Resolution | 1936 (H) × 1216 (V) |
| Spectral range | 300 to 1100 nm |
| Sensor | Sony IMX174 |
| Sensor type | CMOS |
| Shutter mode | GS (Global shutter) |
| Sensor size | Type 1/1.2 |
| Pixel size | 5.86 μm × 5.86 μm |
| Lens mount | C-Mount |
| Optical Filter | Type Hoya C5000 IR cut filter |
| Max. frame rate at full resolution | 155 fps at 450 MByte/s, Mono8 |
| ADC | 12 Bit |
| Image buffer (RAM) | 256 KByte |
| Non-volatile memory (Flash) | 1024 KByte |

Imaging performance

Imaging performance data is based on the evaluation methods in the EMVA 1288 Release 3.1 standard for characterization of image sensors and cameras. Measurements are typical values for monochrome models measured without optical filter.

Output

| | |
|---------------------------------|--|
| Bit depth | 10-bit, 12-bit; Adaptive (10-bit, 12-bit) |
| Monochrome pixel formats | Mono8, Mono10, Mono10p, Mono12, Mono12p |
| YUV color pixel formats | YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr |
| RGB color pixel formats | RGB8 (default), BGR8 |
| Raw color pixel formats (Bayer) | BayerRG8, BayerRG10, BayerRG10p, BayerRG12, BayerRG12p |

Features

Image control: Auto

- Auto exposure
- Auto gain
- Auto white balance (color models)

Image control: Other

- Adaptive noise correction
- Binning (digital)
- Black level
- Color transformation (incl. hue, saturation; color models)
- Contrast
- Custom convolution
- De-Bayering up to 5×5 (color models)
- DPC (defect pixel correction)
- Gamma
- Lens shading correction
- LUT (look-up table)
- Multiple ROIs (regions of interest)
- Reverse X/Y
- ROI (region of interest)
- Sharpness/Blur

Camera control

- Acquisition frame rate
- Bandwidth control
- Counters and timers
- Event channel
- Firmware update in the field
- I/O and trigger control
- Image chunk data
- Power Saving Mode
- Readout modes (SensorBitDepth)
- Sequencer
- Serial I/Os
- Temperature monitoring
- User sets

.ai für TechDoc auf prodata alvium tech doc ablegen

