

Alvium

GM2-203



- IMX422 CMOS sensor
- ALVIUM image processing
- GMSL2 interface
- Various hardware options

Model without hardware options

Alvium GM2: Benefit from greater flexibility in speed and range

CSI-2 based Alvium cameras with GMSL2™ interface

Alvium GM2 cameras with GMSL2™ (Gigabit Multimedia Serial Link) interface have been designed to overcome the limitations of standard CSI-2 cameras. With a large choice of over 30 high-quality CMOS global and rolling shutter sensors Allied Vision is offering the broadest variety of GMSL2™ cameras in the market. The CSI-2 based closed housing cameras come with an integrated serializer, 2 GPIOs (General Purpose Input/Output) on the camera and two rugged interface connectors to choose from.

To operate Alvium GM2 cameras on your vision system, Allied Vision provides different access modes:

- **GenICam for CSI-2 Access** controls the camera by GenICam features, using the Alvium CSI-2 driver and CSI-2 transport layer (TL) directly. Alvium GM2 models with equivalent 1800 C models are supported. Please find FAQs and installation instructions in the [Getting Started with GenICam for CSI-2](#) application note.
- **Direct Register Access (DRA)** to control the cameras via registers for advanced users.
- **Video4Linux2 Access** allows to control the cameras via established V4L2 API and applications like GStreamer and OpenCV. Open-source CSI-2 drivers are available on [GitHub](#) for different boards and system on chips (SoCs).

In addition to lens mount and housing options, see [Customization and OEM Solutions webpage](#) for additional options.

Specifications

| | |
|------------------------------------|--|
| Interface | GMSL2, based on MIPI CSI-2, up to 4 lanes |
| Resolution | 1632 (H) × 1248 (V) |
| Spectral range | 300 to 1100 nm |
| Sensor | Sony IMX422 |
| Sensor type | CMOS |
| Shutter mode | GS (Global shutter) |
| Sensor size | Type 1/1.7 |
| Pixel size | 4.5 μm × 4.5 μm |
| Lens mounts (available) | C-Mount, CS-Mount |
| Max. frame rate at full resolution | Mainly depends on hardware and register settings |
| ADC | 12 Bit |
| Image buffer (RAM) | 256 KByte |
| Non-volatile memory (Flash) | 1024 KByte |

Output

| | |
|---------------------------------|--|
| Bit depth | 8-bit, 10-bit, 12-bit; Adaptive (10-bit, 12-bit) |
| Monochrome pixel formats | PFNC: Mono8, Mono10, Mono10p, Mono12, Mono12p CSI-2: RAW8, RAW10, RAW12 FOURCC: GREY, Y10, Y12 |
| YUV color pixel formats | PFNC: YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr CSI-2: YUV422 8-bit FOURCC: UYVY |
| RGB color pixel formats | PFNC: RGB8 (default), BGR8 CSI-2: RGB888 (default) FOURCC: RGB3 |
| Raw color pixel formats (Bayer) | PFNC: BayerGR8, BayerGR10, BayerGR10p, BayerGR12, BayerGR12p |

General purpose inputs/outputs (GPIOs)


| | |
|----------|----------------------|
| TTL I/Os | 2 programmable GPIOs |
|----------|----------------------|

Operating conditions/dimensions

| | |
|-------------------------|----------------------------|
| Operating temperature | -20 °C to +65 °C (housing) |
| Power requirements (DC) | 5 VDC over MIPI CSI-2 |

| | |
|-----------------------------------|--|
| Power consumption | Value for the integrated serializer adds to CSI-2 model value. |
| Mass | 70 g |
| Body dimensions (L × W × H in mm) | 41 × 29 × 29 |

Quantum efficiency



Features

Image control: Auto

- Auto exposure
- Auto gain
- Auto white balance (color models)

Image control: Other

- Adaptive noise correction*
- Binning (digital)
- Binning (digital, sensor)*
- Black level
- Color transformation (incl. hue, saturation; color models)
- Contrast*
- Custom convolution*
- De-Bayering up to 5×5 (color models)
- DPC (defect pixel correction)
- Gamma
- Lens shading correction*
- LUT (look-up table)*
- Reverse X/Y
- ROI (region of interest)
- Sharpness/Blur*

Camera control

- Acquisition frame rate
- Counters and timers*
- Firmware update in the field
- I/O and trigger control
- Image chunk data*
- Readout modes (SensorBitDepth)*
- Serial I/Os*
- Temperature monitoring
- User sets*

*GenICam for CSI-2 Access

Technical drawing

