


Prosilica GB 2450



- Single board
- 15.1 fps @ full resolution
- Landscape sensor orientation
- Auto-iris (video type)

Landscape or portrait sensor orientation

Single-board OEM cameras with Gigabit Ethernet interface

Prosilica GB 2450 with Sony ICX625 runs 15.1 frames per second at 5.0 MP resolution.

Prosilica GB Gigabit Ethernet CCD cameras are single-board versions of our popular **GC** GigE Vision cameras. The credit card-sized Prosilica GB are high-performance machine vision cameras with Gigabit Ethernet interface (GigE Vision®).


- Ultra-compact size (2" x 3.5")
- VGA to 5 Megapixel resolution
- Fast frame rates to 120 fps
- Optional vertical connector orientation
- Portrait or landscape sensor orientation

Specifications

Prosilica GB 2450	
Interface	IEEE 802.3 1000baseT
Resolution	2448 (H) × 2050 (V)
Sensor	Sony ICX625
Sensor type	CCD Progressive
Shutter mode	Global shutter
Sensor size	Type 2/3

Prosilica GB 2450	
Pixel size	3.45 μm \times 3.45 μm
Lens mount (default)	C-Mount
Max. frame rate at full resolution	15.1 fps
ADC	14 Bit
Image buffer (RAM)	16 MByte
Output	
Bit depth	8/12 Bit
Monochrome pixel formats	Mono8, Mono12, Mono12Packed
YUV color pixel formats	YUV411Packed, YUV422Packed, YUV444Packed
RGB color pixel formats	RGB8Packed, BGR8Packed
Raw pixel formats	BayerRG8, BayerRG12, BayerGR12Packed
General purpose inputs/outputs (GPIOs)	
TTL I/Os	1 input, 1 output
Opto-isolated I/Os	1 input, 1 output
RS232	1
Operating conditions/dimensions	
Operating temperature	0 $^{\circ}\text{C}$ to +70 $^{\circ}\text{C}$ ambient (without condensation)
Power requirements (DC)	5 to 25 VDC
Power consumption	3.8 V at 12 VDC
Mass	54 g
Body dimensions (L \times W \times H in mm)	51 \times 89 (board-size W \times L)
Regulations	2011/65/EU, including amendment 2015/863/EU (RoHS)

Quantum efficiency



Features

Image optimization features:

- Auto gain (manual gain control: 0 to 30 dB; 1 dB increments)
- Auto exposure (manual exposure control: 10 μ s to 42.9 s; 1 μ s increments)
- Auto white balance (GB2450C only)
- Binning (sum)
- Region of interest (ROI), DSP subregion (selectable ROI for auto features)

Camera control features:

- Auto-iris (video type)
- Event channel
- Global shutter (digital shutter)

- Image chunk data
- Recorder and Multiframe acquisition modes
- RS232
- Storable user sets
- StreamBytesPerSecond (bandwidth control)
- Stream hold
- Sync out modes: Trigger ready, input, exposing, readout, imaging, strobe, GPO

Applications

Prosilica GB2450 is ideal for a wide range of applications including:

- LCD panel inspection
- High-resolution industrial inspection
- 3D metrologyGeneral machine vision
- Public security
- Surveillance
- Intelligent Traffic Systems (ITS)
- Embedded systems
- OEM applications